


USPE Left-Sink Autopsy Station

ORIGINAL USPE CONFIGURATION SIGN-OFF | UNSIGNED / NOT FOR FABRICATION

FRONT



CAD ASSEMBLY



Model / drawing: USPE-AS-L-WM

PROPOSED CAD ENVELOPE

X across drawing: 2,133.6 mm
Y front-to-back: 906.6 mm
Z overall: 1,079.4 mm

Includes modeled fixtures and overhangs. This is not an approved product-dimension schedule. Views not to scale.

REVIEW BEFORE ACCEPTANCE

- [] Quantity and exact configuration
- [] Overall and working dimensions
- [] Clearances and accessory mounting
- [] Materials / selected purchased parts
- [] Utilities, drainage and ventilation
- [] Loads, supports and safety review
- [] Image and document revision match

Configuration acceptance:

Name: _____

Signature: _____

Date / quote reference: _____

Engineering and IP/legal approvals remain separate. No signature or approval has been supplied.

TOP



RIGHT



REFERENCE VIEWS FROM THE SAME EDITABLE CAD ASSEMBLY

Purchased components are layout proposals. Ratings, compatibility and approvals must be verified.
Customer configuration acceptance does not authorize manufacture or certify safety / compliance.